


Inspections

Digital wear measurement for mixers



The **Digital GAP Measurement** provides a precise digital assessment of chamber wear using multiple measuring points distributed throughout the mixing chamber. Complementing this, the **3D Rotor Scan** captures the exact rotor geometry and enables comparison with previous measurements.

Together, these technologies provide an accurate assessment of the current condition of both the rotor and the chamber while precisely determining the current mixer free volume. The combined data enables significantly more accurate condition monitoring and lifetime prediction.

[Digital gap measurement for internal mixers](#)



[3D digitisation of built-in mixer rotors](#)

[High precision wear measurement services](#)



Your benefits

- Accurate condition assessment
- Improved lifetime prediction
- Optimised maintenance planning
- Reduced downtime

